




CERTIFICATION, TROUBLESHOOTING, and INSTALLATION tools
for professionals who install and maintain critical network infrastructure.

Featured copper cable test solutions

www.flukenetworks.com/copper



LinkIQ™ Cable+Wi-Fi+Network Testers

- Cable performance testing up to 10GBASE-T plus troubleshooting (distance to fault, wire map, toning)
- IPv4 and v6 ping, nearest switch diagnostics (IP address, name, port / VLAN number, and advertised data rates).
- Ethernet Alliance certified PoE Verification – detects the PoE class (1-8) and power, performs a load test
- Wi-Fi analysis to Wi-Fi 6E, including networks, channels, and access points (Duo models)
- Manage results and print reports from LinkWare™ PC



Add capabilities with our LinkIQ kits:

- Connect to 1 and 10 Gb/s fiber networks
- Identify and trace copper or fiber cables
- Inspect for and solve fiber contamination issues
- Measure fiber optic power levels and loss
- Check fiber transceivers and polarity
- Pinpoint coax or fiber faults
- Cut, strip, and terminate copper cabling

www.flukenetworks.com/LIQ_Kits for more information

MicroScanner™ Series

- Displays cable length, wire map, cable ID, and distance to fault
- Displays PoE class (1-8), power (to 90W) and voltage (MS-PoE)
- Locate and trace cables with IntelliTone™ or Pro3000 probes
- Tests RJ11, RJ45, and coax
- Displays network switch speeds up to 10G
- Ethernet Alliance PoE Certified for faster and easier integration



MicroMapper™

- Verify correct and erroneous wire map
- Tests twisted pair cables for open circuits, shorts, crossed pairs, reversed pairs and split pairs
- Remote identifier enables one-person testing
- Locate and trace cabling with Pro3000 probe



Fiber fault location, power meters, and light sources

www.flukenetworks.com/fiber



MultiFiber™ Pro MPO Loss Tester

- Automatic scanning and testing of 8 or 12 fibers in MPO connectors
- MM and SM versions available
- Cuts MPO test time 70% or more
- Automatically measures and reports polarity



FiberLert™ Live Fiber Detector

- Light and sound indicate presence of optical signal (850 to 1625 nm)
- Suitable for ports and patch cords, SM, MM, UPC and APC
- “Non-contact” detector reduces the risk of contamination and damage
- Checks transceivers and polarity



Fiber QuickMap™

- Locates and displays connections and breaks
- Tests MM fiber to 1,500 meters (4,921 ft)
- Simple set-up
- Displays loss and distance to fault



SimpliFiber® Pro Power Meter/Light Source

- Supports single-mode and multimode
- Measures and stores two wavelengths at once in a single record for faster testing
- Min/Max capability tracks intermittent power fluctuations



VisiFault™ Visual Fault Locator

- Locates tight bends, breaks and bad connectors
- Verifies polarity and identifies fibers
- Continuous and flashing modes
- Rugged design



Copper cable toners and probes

www.flukenetworks.com/tone

Pro3000™ Analog Toner and Probe Family

- Filter technology blocks annoying “buzz”
- Identifies pairs with SmartTone™
- 10 mi (16 km) range
- Tones through drywall, wood, and other enclosures
- Angled bed-of-nails clips and RJ-11 connector



TS™ Series Fault Finders

- Supports two-conductor cables up to 915 m (3,000 ft.)
- Displays distance to end or fault
- SmartTone™ positively identifies pair



IntelliTone™ Pro 200 LAN Toner and Probe

- Digital toning eliminates noise and false signals
- Identify pairs with SmartTone™
- Locates active networks
- Visible end-to-end continuity test
- Built in wire mapper
- Works on twisted pair, audio, and video cabling



www.FlukeNetworks.com/contact

Fiber cleaning and inspection

www.flukenetworks.com/inspect



Fiber Optic Cleaning Kits

- Eliminates the #1 cause of fiber failure: contamination
- Supports wide variety of connectors
- Quick Cleaners for end-faces and ports
- Fiber solvent and cleaning cards leave no residue or dust



Quick Clean™ Cleaners

- Available in 1.25 mm, 2.5 mm, and MPO styles
- Clean over 500 end-faces per unit
- Tip extender to 208 mm for hard-to-reach connectors



FI-500 FiberInspector™ Micro

- PortBright™ illumination for dark panels
- Auto-focus
- Clearly displays MM and SM
- Includes four UPC tips; APC available



See page 4 for our MPO Inspection Solution

Test Reference Cords (TRCs) and OTDR Launch Cables

- Standards-compliant with reference grade connectors
- Durable metal LC connectors
- Launch fibers feature a rugged, convenient zipper case



Hand tools

www.flukenetworks.com/tools

D914™ Series Impact Tools

- Hook, spudger and blade storage built-in
- Adjustable impact for different wire gauges
- Optional screwdriver, sockets and bits



JackRapid™ Punchdown Tool

- Eight times faster than traditional impact tools.
- Convenient, built-in stripper
- Adapters for a variety of vendors' jacks



Pro-Tool™ Kits

- Dur-a-Grip™ pouch and belt clip keeps tools handy
- Available with impact tool, D-Snips™, cable stripper, and flashlight



Modular Crimper



Need-L-Lock™ Crimping Pliers



D-Snips™



Cable Strippers



Probe Pic



Can Wrenches



4 and 8 position Modular Adapters

Telephone butt-in test sets

www.flukenetworks.com/telco



TS™54, combines advanced test set, toner, TDR and pair identifier in military grade rugged package



TS™52PRO, military-grade ruggedness with display and advanced features



TS™22 Series, rugged design with time-saving features



TS™30 Series, rugged design priced right



TS™25D, feature-rich design for DSL installs

www.FlukeNetworks.com/contact

VERSIV™

www.flukenetworks.com/Versiv

- ProjX Management System streamlines testing and prevents errors
- Built-in “Fault Info” pinpoints even complex failures
- Worldwide support team with 100+ years of experience
- 1,000+ how-to articles and videos
- Legendary Fluke ruggedness and reliability



Certify and Troubleshoot

DSX CableAnalyzer™ Series Copper Certification

Meets the most stringent TIA and IEC accuracy requirements. Endorsed by 30+ cable manufacturers; supports hundreds of cable types and standards.



Manage the Process: LinkWare™ Live

Upload test results over Wi-Fi and consolidate results across multiple testers. Create and manage test setups and ID's. Track results, last used location, and calibration status online.



CertiFiber™ Pro

Certifies two fibers at two wavelengths in under three seconds. “Set Reference” wizard prevents common setup errors.



Document Results: LinkWare PC

Save, maintain, and share test results. Generate professional, customizable reports with the industry's de facto reporting standard.



OptiFiber™ Pro

Automated setup and analysis quickly identifies events in LANs, datacenters, PON, and FTTx.



Become an Expert: CCT

The 10,000 graduates of our Certified Cabling Test Technician™ program finish jobs faster, avoid mistakes, and deliver results accepted by manufacturers and customers. The two-day course covers copper and fiber; earns 14 BICSI CECs.

www.flukenetworks.com/cctt



FiberInspector™ Pro

Automated pass/fail testing of single fiber end faces.



FiberInspector™ Ultra

Automated pass/fail testing of MPO and single fiber end faces with Versiv or smartphone.



Reduce Support Costs: Fluke Premium Care

Minimize downtime and optimize ROI with a comprehensive service agreement that includes priority service, extended warranty coverage, calibration assistance, and access to loaner units during repairs.

www.flukenetworks.com/gold-product-support

