


**NEW YEAR
NEW GEAR**

25

FLUKE®

3 DEC 2024 - 28 FEB 2025

THE BEST JUST GOT BETTER



NEW

Fluke 1670 Series Multifunction Installation Testers



Learn more:

fluke.co/1670nyng25

Faster installation testing, documentation and reporting with accuracy you can trust.



Effortless setup with a streamlined interface and full-colour touchscreen.



Boost accuracy and speed with Auto Test and Automatic Measurement Validation.



Streamline reports with automatic population and one-touch reporting via Fluke TruTest™.

BONUS

HAND TOOLS STARTER KIT

WHEN YOU SPEND \$3000+

SPEND \$3,000 OR MORE

in a single transaction on Fluke tools featured in this promotion and get a bonus Fluke Insulated Hand Tools Starter Kit.

Offer available while stocks last. Terms and Conditions apply.



Valued at \$425.00

REDEMPTION OFFERS INSIDE →


Fluke Digital Multimeters



Fluke 115/116/117 Digital Multimeters


Fluke digital multimeters are on more toolbelts, finding more problems, than any other comparable test tools. Every Fluke digital multimeter gives you what you need: accurate measurements; consistent, reliable performance; safety; and the strongest warranty available.


	115	116	117
	Field Service Testing Multimeter	HVAC Multimeter with temperature and microamp	Electricians Multimeter with non contact Voltage
True-RMS readings	AC	AC	AC
Display backlight	•	•	•
Built-in thermometer		•	
Loz (low input impedance)		•	•
Frequency/capacitance/diode test	•/•/•	•/•/•	•/•/•
Safety rating	CAT III 600 V	CAT III 600 V	CAT III 600 V



Buy a Fluke 115 and receive a FREE:
Fluke ST240+ RCD Socket Tester


Valued at \$68.00





Buy a Fluke 116 or 117 and receive a FREE:
Fluke C116 Soft Carry Case + Fluke ST240+ RCD Socket Tester


Valued at \$185.00



Fluke 179 True-RMS Digital Multimeter

Versatile, industry-standard multimeter with a lifetime warranty.

- True-RMS voltage and current measurements
- Basic accuracy of 0.09%
- Temperature measurements



Fluke 87V MAX Industrial Multimeter

Rugged, waterproof, accurate multimeter for harsh environments.

- Waterproof, dust-proof IP67 case; withstands drops up to 4-metres
- Supports accurate measurements on VFDs using a low-pass filter
- Captures intermittents as fast as 250 μ S with peak capture



Buy a Fluke 179 True-RMS Digital Multimeter and receive a FREE:
Fluke TLK-220 SureGrip™ Industrial Test Lead

Valued at \$374.00





Buy a Fluke 87V MAX Industrial Multimeter and receive a FREE:
Fluke TLK-225 SureGrip™ Master Accessory Set

Valued at \$374.00




Fluke Electrical Testers



Fluke Electrical Testers

Fluke open fork testers enable you to measure current, voltage, continuity and resistance quickly and safely. When you need fast answers to solve difficult problems, the Fluke Electrical Testers will be your first choice.


	T5-1000	T6-1000	T6-1000 PRO
Visual Continuity™			•
FieldSense™ voltage measurement technology		•	•
Safety Rating	CAT III 1000V	CAT III 1000V CAT IV 600V	CAT III 1000V CAT IV 600V
Voltage AC/DC	1000 V	1000 V	1000 V
Current AC	100 A	200 A	200 A
Resistance/Frequency	1000 Ω	100 kΩ/45-66 Hz	100 kΩ/45-66 Hz



Buy a Fluke T5-1000 and receive a FREE:

Fluke ST240+ Socket Tester
+ Dometic 320mL Tumbler

Valued at \$93.00





Buy a Fluke T6-1000 PRO and receive a FREE:

Fluke LVD2 Voltage Tester
+ TPAK Magnetic Hanger

Valued at \$224.00



Fluke Clamp Meters




Fluke Clamp Meters


The Fluke 320 and 370 Series clamp meters deliver reliable and accurate measurements, making them ideal for everything from basic troubleshooting to advanced diagnostics.

	323	325	376 FC	378 FC
Current True-RMS AC		400A		2500A (iFlex® Coil)
Current DC		400A		999.9A
Voltage AC/DC		600 V		1000 V
FieldSense™				•
PQ indicator				•

FieldSense™ Enabled



Measure voltage and current simultaneously with Fluke FieldSense™ for safer and more productive work.*





Buy a Fluke 323 or 325 Clamp Meter receive a FREE:

Fluke TL175 TwistGuard™ Test Lead Set

Valued at \$88.00





Buy a Fluke 376 FC Clamp Meter receive a FREE:

Fluke T5-1000 Voltage, Continuity and Current Tester

Valued at \$400.00





Buy a Fluke 378 FC Clamp Meter receive a FREE:

Fluke t3000 FC Wireless Temperature Module or Fluke Pack30 Tool Backpack

Valued up to \$492.00



* Voltage measurement requires capacitive path to ground. Ground connection via test lead may be required in some situations.

Fluke Insulation Testers

Fluke Insulation Testers

Whether you work on motors, generators, cables, or switch gear, the Fluke digital insulation resistance testers provide noise-free, reliable results. They are designed to be safe, simple to use and gimmick-free for both troubleshooting and preventive maintenance.



Buy a Fluke 1503 or 1507 and receive a FREE:

Fluke 323 True-RMS Clamp Meter

Valued at \$345.00

Buy a Fluke 1587 FC and receive a FREE:

Fluke 325 True-RMS Clamp Meter

Valued at \$478.00

Fluke Installation Testers



Fluke Multifunction Installation Testers

Fluke's Multifunction Installation Testers provide reliable verification of electrical installation safety across domestic, commercial, and industrial settings. They are easy to use and ensure that fixed wiring is safe and correctly installed to meet local standards.

	1662 AU	1672 <small>NEW</small>	1673 FC <small>NEW</small>	1674 FC <small>NEW</small>
Insulation PreTest™ safety function				•
Fluke Connect® compatibility			•	•
RCD trip time	•	•	•	•
Full-colour touch screen		•	•	•
User-programmable auto test sequence				•
Template integration with TruTest™ Software		•	•	•
Auto pass/fail results		•	•	•
EV test 6 ma DC			•	•

Buy a Fluke 1662/AU Multifunction Installation Tester and receive a FREE:

Fluke 323 True-RMS Clamp Meter

Valued at \$345.00

TruTest™ Software Integration

Fluke TruTest™ software simplifies data management and cuts documentation time by up to 50%. Easily link test results, generate inspection certificates on-site, and invoice immediately.

Fluke Thermal Cameras

Fluke Entry Level Thermal Cameras

Fluke offers a range of entry-level thermal imaging solutions for diverse users, from home enthusiasts to technicians. Whether for minor electrical inspections or advanced analysis, our thermal cameras deliver performance and reliability.

Tailored For DIY

Fluke iSee™ Mobile Thermal Camera



- Perfect for easy tasks like home and minor electrical inspections
- Affordable and user-friendly
- Lightweight and portable design for easy handling

Buy a Fluke TC01A or TC01B Mobile Thermal Camera and receive a FREE:


Fluke iSee™ Thermal Camera Pouch & Fluke Bottle Opener



EXCLUSIVE

Tailored For Tradesmen

Fluke PTi120 Thermal Camera



- Ideal for users needing quick thermal inspections with analysis and reporting
- Pocket-sized for on-the-go inspections
- Features Fluke Connect Asset Tagging and IR-Fusion™

Buy a Fluke PTi120 Thermal Camera and receive a FREE:

Fluke IKSC7 Insulated 7 Piece Screwdriver Kit



Valued at \$154.00

Tailored For Technicians

Fluke TiS20+ MAX Thermal Camera



- Tailored for technicians needing advanced capabilities and reporting
- Features Fluke Connect Asset Tagging and IR-Fusion™
- Includes a spare battery pack (2 total)

Buy a Fluke TiS20+ MAX Thermal Camera and receive a FREE:

Fluke Pack30 Professional Tool Backpack



Valued at \$443.00

Fluke Ethernet Cable Testers



Fluke Networks LinkIQ™ Series

Fluke Networks LinkIQ™ testers are fast, reliable, and built to handle the toughest demands. These user-friendly tools streamline network diagnostics, ensuring quick validation and seamless operations.



Buy a Fluke Networks LinkIQ™ Cable + Network Tester or Kit and receive a FREE:

Fluke Pack30 Professional Tool Backpack

Valued at \$443.00



Buy a Fluke Networks LinkIQ™ Industrial Ethernet Tester or Kit and receive a FREE:

Fluke Pack30 Professional Tool Backpack + Sonos Roam Portable Bluetooth Speaker

Valued at \$743.00



NYNG 25

3 DEC 2024– 28 FEB 2025

Fluke Renewable Energy Solutions



Fluke FEV300 EV Charging Station Test Adapter

Test the functionality and safety of electrical vehicle charging stations, easily and reliably.

- Vehicle simulation: CP Control Pilot state simulation tests different charging states
- Grounding protection: PE Pre-Test for dangerous voltage
- GFCI testing: Stay protected from and check risk of electric shock



Buy a Fluke FEV300 EV Charging Station Test Adapter Kit* and receive a FREE:

Fluke 87V MAX Industrial Multimeter

Valued at \$1,300.00

* Offer valid only for kit featuring 1664 FC+ Installation Tester and Type 2 Connector.



Fluke SMFT-1000 PRO Multifunction PV Tester and Performance Analyser, I-V Curve Tracer

Your all-in-one test solution to verify PV system performance.

- Wireless Irradiance Meter: no leads required
- Instant on-site I-V curve comparison
- Record visual inspections, then manage data with TruTest™ Solar Software



Buy a Fluke SMFT-1000 PRO Multifunction PV Tester and Performance Analyser, I-V Curve Tracer and receive a FREE:

Fluke 393 FC Clamp Meter

Valued at \$1,496.00



How to redeem your FREE bonus:

- 1 Purchase an eligible Fluke test tool between **3 December 2024 and 28 February 2025**.
- 2 Visit ➔ fluke.co/nyng25 or scan the QR code to redeem.



Sponsored by Fluke Australia Pty Ltd. Prices are recommended trade prices. Final pricing at the discretion of authorised Fluke Australia distributors. Purchases must be made between **3 December 2024 and 28 February 2025** or while stocks last. To redeem the Fluke Insulated Hand Tools Starter Kit, spend \$3,000.00 (incl. GST) in a single transaction on eligible Fluke products featured in the promotion, including the new Fluke 1670 Series. Customers purchasing via a wholesaler branch must ensure the branch is purchasing from a Fluke Australia authorised distributor. For a list of authorised distributors, visit www.fluke.com/en-au/where-to-buy. Redeem online with proof of purchase at fluke.co/nyng25 by 14 March 2025. Fluke reserves the right to verify purchase and eligibility before processing redemption. Offer is non-transferable, not redeemable for cash, and may be modified or terminated by Fluke at any time. Delivery may take 6-12 weeks. Offers available to Australian and New Zealand residents only. Offers cannot be combined with any other discounts, promotions, or special offers.