

**FLUKE**

NEW accessory
NEW application
NEW price

Capture every detail:

**The ii500 Acoustic Imaging Camera.
NOW more affordable than ever!**

Fluke ii500 Acoustic Imager with LeakQ™: Detect, Locate, and Capture Gas Leaks

Key features

- **Ready-to-Use:** The Fluke ii500 is ready out of the box. Its rugged, ergonomic design ensures easy handling.
- **Quick Detection:** Even users with minimal experience can start detecting leaks within minutes. The tool estimates relative leak size and cost, incorporating a new distance-estimation feature and the 1-10 LeakQ™ severity index.
- **SoundMap™ Overlay:** The 7" LCD touchscreen overlays a SoundMap™ on visual images, facilitating rapid leak location identification.
- **Intuitive Interface:** Easily isolate leak sound frequencies and filter out background noise.
- **Tagging and Organization:** Use image and video tagging, annotation, and folders for efficient organization.
- **Leak Sizing:** Prioritize repairs based on relative leak size.

New accessory*:

Ensure the integrity of your non-pressurized vessels with the **Fluke SB140 Sound Beacon**.

Now available at a reduced price.

Improve your leak detection capabilities with the **ii500 Acoustic Imager**—now available at a reduced price—paired with the **Fluke SB 140 Sound Beacon** for optimized performance.



Get your Acoustic Imager now!

Valid from June 1st 2025.

Speak to your Fluke specialist for more information.