

More efficiency by smarter testing

**Promotional
period:**
01.09.2025 -
19.12.2025

Contact us today for your offer

Maximize efficiency and minimize costs on every job with exclusive savings on the most advanced testing and certification solutions.

Specialist Kit #1

High accuracy network test solution offering comprehensive standards compliance and certification up to Cat6A and Class FA.

Save 18,911kr

Item # 4955017 |
Part # DSX2-5000/GLD INT

+ Gold
Support



Specialist Kit #2

High accuracy network test solution offering comprehensive standards compliance and certification up to Cat8 and Class I/II.

Save 32,922kr

Item # 4954550 |
Part # DSX2-8000/GLD INT

+ Gold
Support



Advanced Kit #1

Designed for testing and certifying copper and fiber cabling systems, the DSX2-5000QI certifies copper to Cat6A and Class FA. It includes Quad Optical Loss Test Set modules with a fiber inspection scope.

Save 28,927kr

Item # 4955074 |
Part # DSX2-5000QI/G INT

+ Gold
Support



Advanced Kit #2

Designed for testing and certifying copper and fiber cabling systems, the DSX2-8000QI certifies copper to Cat8 and Class I/II. It includes Quad Optical Loss Test Set modules with a fiber inspection scope.

Save 31,623kr

Item # 4954687 |
Part # DSX2-8000QI/G INT

+ Gold
Support



Advanced Kit #3

A complete solution for testing and certifying copper and fiber cabling systems. The DSX2-8000QOI certifies copper to Cat8 and Class I/II. It includes Fiber Quad Optical Loss Test Set modules and a Quad OTDR module with a fiber inspection scope.

Save 70,007kr

Item # 4954610 |
Part # DSX2-8000QOI/G INT

+ Gold
Support



Intro Kit

Essential test and certification solution for twisted pair structured copper cabling up to Cat6A.

Save 13,758kr

Item no. 6008226 |
Part no. DSX-602-PRO/GLD

+ Gold
Support



COPPER



Fiber Kit #1

High performance solution which accelerates every step of the fiber certification process, comprising a Quad Optical Loss Test Set.

Save 24,771kr

Item # 4955805 |
Part # CFP2-100-Q/GLD INT

+Gold Support



Fiber Kit #2

High performance solution comprising a Quad Optical Time Domain Reflectometer (OTDR) and fiber inspection scope for troubleshooting and certification.

Save 26,006kr

Item # 4955462 |
Part # OFP2-100QI/GLD INT

+Gold Support



FIBER



Fiber Kit #3

Enhance your existing DSX Copper Series (DSX2-5000/ DSX2-8000) and deliver industry-leading efficiency for optical loss certification across both multimode and single mode fibers.

Save 24,024kr

Item # 4334851 |
Part # CFP-Q-Add



COPPER



FIBER



GOLD SUPPORT

Premium Care – Gold Support

Premium Care is our comprehensive maintenance program for Fluke Network's products.

It provides unmatched support for customers wanting to minimize business downtime and ensure a high return on investment. The service agreement includes annual calibration (where relevant), replacement accessories, repairs with priority service, and access to loaner units during repairs. Gold support is included for select discounted products or can be purchased separately. Contact your Fluke Networks representative today to find out more.

Read more:

www.flukenetworks.com/content/gold-product-support

*Terms and conditions apply. The discount offered under this promotion is valid on purchases of qualifying products made from Fluke's authorized distributors only. Our authorized distributors are free to provide additional price discounts and, thus, higher end-customer savings. Promotion sponsor: Fluke Europe BV. For more information, call: +44-(0)20-79420721, +31-(0)20-7132984, or email: info@flukenetworks.com

