

Tested. Trusted. Ready for anything.

Save up to 85,000 DKK

on Fluke Networks' most advanced fiber and copper certification and troubleshooting kits – built for accuracy, speed and reliability on every job.

Contact us
for your offer
today

Promotional period: 01.09.2026 – 18.12.2026

Limited-time savings on best-selling fiber and copper certification and troubleshooting solutions. Choose the tools that match your workflow.



CertiFiber™ Pro Quad OLTS Kit

A complete solution for fast, accurate certification of singlemode and multimode fiber links to industry standards.

Category: Fiber
Item no. 4955805
Part no. CFP2-100-Q/GLD INT

Save 31,742 DKK



OptiFiber™ Pro OTDR Kit

A troubleshooting and extended testing solution that locates faults, loss and reflections in fiber links.

Category: Fiber
Item no. 4955462
Part no. OFP2-100QI/GLD INT

Save 32,195 DKK



CertiFiber™ Pro Add-On Kit

An upgrade kit that adds fiber certification capability to an existing Versiv™ mainframe and remote test setup (for use with DSX-5000 and DSX-8000 series).

Category: Fiber
Item no. 4334851
Part no. CFP-Q-Add

Save 28,885 DKK



DSX2-5000QI CableAnalyzer™ Kit

A copper and fiber certification and inspection solution for testing networks up to 10 Gigabit Ethernet.

Category: Copper and Fiber Kit
Item no. 4955074
Part no. DSX2-5000QI/G INT

Save 38,540 DKK



DSX2-8000QI CableAnalyzer™ Kit

A high-performance copper and fiber cable certification and inspection solution designed for high-speed networks.

Category: Copper and Fiber Kit
Item no. 4954687
Part no. DSX2-8000QI/G INT

Save 42,067 DKK



DSX2-8000QOI CableAnalyzer™ Kit

An advanced all-in-one certification kit combining copper and fiber certification, OTDR troubleshooting and fiber inspection in a single solution.

Category: Copper and Fiber Kit
Item no. 4954610
Part no. DSX2-8000QOI/G INT

Save 85,332 DKK



DSX-602-PRO CableAnalyzer™ Kit

Essential test and certification solution for twisted pair structured copper cabling up to Cat 6A with fast 10-second tests.

Category: Copper
Item no. 6008226
Part no. DSX-602-PRO/GLD

Save 15,151 DKK

Savings shown against regular list prices. Savings vary by configuration. More offers available on Page 2.

Talk to Fluke Networks to build your confidence and consistency in every fiber and copper installation.



DSX2-5000 CableAnalyzer™ Kit

High accuracy network test solution offering comprehensive standards compliance and certification up to Cat6a and Class FA.

Category: Copper

Item no. 4955017

Part no. DSX2-5000/GLD INT

Save 21,846 DKK



DSX2-8000 CableAnalyzer™ Kit

High-performance copper certification up to Cat8 and Class I/II for the most demanding networks.

Category: Copper

Item no. 4954550

Part no. DSX2-8000/GLD INT

Save 36,580 DKK



Why choose Fluke Networks?

From enabling hyperscale data centers to connecting transportation, utilities, smart cities and renewable energy infrastructure, fiber and copper networks are the backbone of the world's most critical projects.

When failure isn't an option, professionals rely on Fluke Networks to deliver measurements they can count on – no matter if it's carrying out diagnostics in the harshest climates to certifying the largest data centers.

Every test matters, and every result determines the resilience of vital communications.

Our fiber and copper solutions are rigorously tested to offer reliable performance and accuracy, ensuring you are ready for anything that your network demands today, and in the future. With our advanced test tools you can:

- Certify fiber and copper faster with confidence
- Reduce retesting, rework and costly call-backs
- Deliver professional reports that build customer trust
- Scale easily as networks grow in speed and complexity, starting with Cat 6A copper to next-generation fiber

From offshore wind farms to smart cities, Fluke Networks has you covered.

Reduce Risk with Premium Care – Gold Support

Fiber and copper testing tools are mission critical. Premium Care – Gold ensures they're always ready when you need them.


Gold support reduces total cost of ownership by:

- Eliminating unexpected service and support charges
- Covering repair or replacement of damaged accessories
- Including annual calibration or performance testing
- Providing loan units to minimize downtime

Less downtime and fewer surprises will give you and your team more confidence on every job.

PremiumCare

Uptime Protection by



From extreme environments to everyday installations, Fluke Networks fiber solutions are tested, trusted, and ready for anything.

- Deliver professional results
- Win more business
- Support the next wave of digital transformation

Discover the fiber solutions that professionals rely on. **Contact Fluke Networks** to learn more.



Fluke. Keeping your world up and running.™

[FlukeNetworks.com](https://www.flukenetworks.com)

©2026 Fluke Corporation
Specification subject to change without notice
260624-en DKK

Modification of this document is not permitted without written permission from Fluke Corporation.