

Technical Data

Fluke 972B/972ES Temperature Humidity Meter



Multiple records, Measure-and-view.

- Clean room
- Indoor environmental quality (IEQ)
- Temperature and humidity verification
- **Equipment and production inspection**

Measure-and-view, industrial design, necessity for inspection

Temperature and humidity are two important items for comfort test of indoor air and environment. The Fluke 972Series Temperature Humidity Meter can quickly and easily collect accurate humidity and temperature data. It features streamlined industrial design and is comfortable to hold. Simplified buttons require no complicated operations. The selected high-precision sensors ensure that reliable data is collected. The Fluke 972 Series is an indispensable environmental monitoring tool for facility maintenance and engineering technicians, HVAC service contractors, R&D and manufacturing engineers, and professionals involved in indoor air quality (IAQ) assessments.

- · Two models, with internal and external probes, are available for limited space
- Accuracy of ± 0.4 °C and ± 3% RH, to meet industrial grade testing requirements
- 99 sets of stored data, easy to review (Fluke 972Bonly)
- · Comfortable grip and ergonomic design
- Reinforced sensor protective cover for worry-free operation







Specifications

		972B	972ES
Detailed Specifications			
Sensor Type		Internal + External	External
Temperature Range		-30.0 °C to 70.0 °C (internal sensor); -40.0 °C to 100°C (external sensor)	-40.0 °C to 100 °C
Temperature Accuracy		Internal sensor: ±0.4 °C (-30 °C to 70 °C) External sensor: ±0.4 °C (-40 °C to 90 °C); ±0.5 °C (90 °C to 100 °C)	±0.4 °C (-40 °C to 90 °C); ± 0.5 °C (90 °C to 100 °C)
Temperature Resolution		0.1 °C	
Dew Point Temperature	Range	-40.0 °C to 100 °C	N/A
	Resolution	0.1 °C	N/A
Wet Bulb Temperature	Range	−20.0 °C to 60.0 °C	N/A
	Resolution	0.1 °C	N/A
Humidity	Range	0% to 99.9% RH	
	Accuracy	±3% RH (20% RH to 80% RH @ 25 °C); ± 5% RH (< 20% RH, > 80 % RH @ 25 °C)	
	Resolution	0.1% RH	
Date Storage		Yes. Up to 99 sets	N/A
Display		2-line LCD display, with backlight	No
Auto Off		Power off after 20 min without any operation	N/A
General Specifications			
Temperature	Operating	-30 °C to 70 °C	-40 °C to 70 °C
	Storage	-30 °C to 70 °C, <80% RH (without battery)	-40 °C to 70 °C, <80% RH
Altitude	Operating	2000 m	
	Storage	12000 m	
Relative Humidity	Operating	0% RH to 99% RH	
	Storage	< 80% RH	
Power Supply	Battery Type	2 x AAA Batteries	_
	Battery Life	1000 hrs for continuous operating, backlight off	_
Safety		IEC61010-1, Pollution Degree 2	
Dimensions (L x W x H)		211 × 58 × 40 mm	264 × 33 × 28 mm
Weight		172 g (body)	127 g
Electromagnetic Environment (EMC)		IEC 61326-1: Portable, Electromagnetic Environment; IEC 61326-2-2; CISPR 11: Group 1; Class A	
IP Rating		IEC 60529: IP30, non-operating	
Warranty		1 year	



Ordering Information

Fluke 972B Temperature **Humidity Meter**

Includes:

- The Fluke 972B
- Fluke 972ES external sensor
- Black soft case



Fluke 972ES external temperature/humidity sensor

Includes:

• Fluke 972ES external sensor





Fluke. Keeping your world up and running.®

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call: From other countries +1 (425) 446-5500 Web access: http://www.fluke.com

©2023 Fluke Corporation. 4/2023