

GOLD SUPPORT



# Exclusive savings Future-proof network solutions

Save up to 28% on selected copper and fiber testers for a limited time only.

Fluke Networks has been providing installers, network technicians and warranty providers worldwide with market leading certification testers, renowned for their durability, accuracy, ease of use and reporting capabilities, since 1992. A global leader in certification, troubleshooting and installation tools, we are trusted by the professionals who install and maintain critical network cabling infrastructure. From establishing the most advanced data centers to restoring service on the factory floor, our combination of unmatched reliability and performance ensures our customers can have confidence in their work.

Our Versiv™ modular platform offers the flexibility to test both copper and fiber from any location. Best of all, it is compatible with Linkware-PC, and Linkware™ Live, the

industry's best reporting software. More than 100 million test results have been uploaded by users to Linkware™ Live to prove it. We back this up with Fluke Premium Care – Gold, the most comprehensive support service available, delivering confidence and maintenance cost control in the same package.

Join us in celebrating more than a decade of our Versiv™/DSX platform with savings on our best-selling models, all including Gold support, for a limited time only, from March 1st to June 21st, 2024.

<https://rb.gy/xu6ejw>



## How does it work?

No returns, registrations, or hassles. Simply contact your local distributor and take advantage of these great discounts.



1

Select your model



2

Buy from your local distributor



3

Enjoy instant savings

| Model                | Regular recommended resale price in Euro | Discounted recommended resale price in Euro | Expected savings* in Euro |
|----------------------|--|---|---------------------------|
| DSX-602-PRO/T & Gold | 10193                                    | 8299  | 1894                      |
| DSX2-5000/GLD/T      | 13725                                    | 11599                                       | 2126                      |
| DSX2-8000/GLD/T      | 17161                                    | 14299                                       | 2862                      |
| DSX2-5000QI/GT       | 26709                                    | 22499                                       | 4210                      |
| DSX2-8000QI/GLD/T    | 28987                                    | 24599                                       | 4388                      |
| CFP2-100-Q/GLD/T     | 16832                                    | 14299                                       | 2533                      |
| OFP2-100Q/GLD/T      | 13739                                    | 10299                                       | 3440                      |

\*Note: our authorized distributors are free to provide additional price discounts and, thus, higher end-customer saving.



## Fluke Networks Program

With discounts of up to 28% from our authorized distributors' regular prices, the savings are substantial.

Furthermore, best-selling products in the promotion include Fluke Premium Care – Gold. Gold is our comprehensive support and maintenance program for Fluke Networks products and accessories. It provides a premium level of support to minimize business downtime and ensure a high return on your investment.

[www.flukenetworks.com/content/gold-product-support](http://www.flukenetworks.com/content/gold-product-support)

## Resolve and prevent your network issues with market leading copper testers

Fluke Networks is the industry's most trusted partner for cable testing from Cat. 8 cabling that can support the transmission of data up to 40Gbps over balanced twisted-pair copper cabling.

The DSX CableAnalyzer™ cable testers provide accurate, error-free certification even in complex projects

where multiple teams are involved in the testing process, with varying media types and multiple testing requirements. The DSX is built on our Versiv™ modular design that supports copper certification, fiber optic loss, OTDR testing and fiber end-face inspection in one.



Fluke Networks  
DSX-8000



Fluke Networks  
CertiFiber Pro

## Accelerate every step of your Fiber Certification

Fibers have proven to be a cost-effective and reliable transmission medium, but they are susceptible to contamination and link damage. It can be time consuming and resource-intensive to narrow down the cause of failure. CertiFiber Pro provides you with an optical loss test set with the fastest time to certify.

Our ProjX™ management system ensures all jobs are completed correctly and efficiently and the optical loss test set provides automatic Pass/Fail analysis to industry standards or custom test limits. Both DSX and CertiFiber are compatible with Linkware™ Live cloud-based service and customers can quickly and easily create professional customised PDF reports with LinkWare™ PC.

## Meet the challenges of enterprise fiber optic infrastructures with Optifiber Pro

Using the same Versiv™ mainframe as DSX and Certifiber modules, Optifiber Pro is our user-friendly Optical Time Domain Reflectometer (OTDR). Optifiber pro is optimized for the enterprise, capable of testing both multimode and Singlemode optical fiber links for performance, for certification (with the Certifiber Pro) and for troubleshooting purposes.

A full 'Autotest mode, unique 'EventMap' display, and full-day battery life simplifies testing and delivers results to make every technician a near-expert.



Fluke Networks  
OptiFiber Pro

Terms and conditions apply. This discount is available from March 1 to June 21, 2024, for end customers in the European Union and in the United Kingdom, Switzerland, Norway, Sweden and Denmark (excluding any country to which EU or US trade sanctions apply). The discount offered is valid on purchases of qualifying products, and made from Fluke's participating authorized distributors only, during the discount period. Find an authorized distributor here: <https://www.flukenetworks.com/wheretobuy>