

# More efficiency by smarter testing

**Promotional  
period:**  
01.09.2025 -  
19.12.2025

Contact us today for your offer

Maximize efficiency and minimize costs on every job with exclusive savings on the most advanced testing and certification solutions.

## Specialist Kit 1

High accuracy network test solution offering comprehensive standards compliance and certification up to Cat6A and Class FA.

**Save 30,570kr**

Item no. 4955017 |  
Part no. DSX2-5000/GLD INT

**+ Gold  
Support**



## Specialist Kit 2

High accuracy network test solution offering comprehensive standards compliance and certification up to Cat8 and Class I/II.

**Save 51,219kr**

Item no. 4954550 |  
Part no. DSX2-8000/GLD INT

**+ Gold  
Support**



## Advanced Kit 1

Designed for testing and certifying copper and fiber cabling systems, the DSX2-5000QI certifies copper to Cat6A and Class FA. It includes Quad Optical Loss Test Set modules with a fiber inspection scope.

**Save 48,290kr**

Item no. 4955074 |  
Part no. DSX2-5000QI/G INT

**+ Gold  
Support**



## Advanced Kit 2

Designed for testing and certifying copper and fiber cabling systems, the DSX2-8000QI certifies copper to Cat8 and Class I/II. It includes Quad Optical Loss Test Set modules with a fiber inspection scope.

**Save 52,732kr**

Item no. 4954687 |  
Part no. DSX2-8000QI/G INT

**+ Gold  
Support**



## Advanced Kit 3

A complete solution for testing and certifying copper and fiber cabling systems. The DSX2-8000QOI certifies copper to Cat8 and Class I/II. It includes Fiber Quad Optical Loss Test Set modules and a Quad OTDR module with a fiber inspection scope.

**Save 110,518kr**

Item no. 4954610 |  
Part no. DSX2-8000QOI/G INT

**+ Gold  
Support**



## Intro Kit

Essential test and certification solution for twisted pair structured copper cabling up to Cat6A.

**Save 22,232kr**

Item no. 6008226 |  
Part no. DSX-602-PRO/GLD

**+ Gold  
Support**



COPPER



## Fiber Kit 1

High performance solution which accelerates every step of the fiber certification process, comprising a Quad Optical Loss Test Set.

**Save 39,695kr**

Item no. 4955805 |  
Part no. CFP2-100-Q/GLD INT

**+Gold Support**



## Fiber Kit 2

High performance solution comprising a Quad Optical Time Domain Reflectometer (OTDR) and fiber inspection scope for troubleshooting and certification.

**Save 40,880kr**

Item no. 4955462 |  
Part no. OFP2-100QI/GLD INT

**+Gold Support**



FIBER



## Fiber Kit 3

Enhance your existing DSX Copper Series (DSX2-5000/ DSX2-8000) and deliver industry-leading efficiency for optical loss certification across both multimode and single mode fibers. .

**Save 37,141kr**

Item no. 4334851 |  
Part no. CFP-Q-Add



COPPER



FIBER



**GOLD SUPPORT**

## Premium Care – Gold Support

Premium Care is our comprehensive maintenance program for Fluke Network's products.

It provides unmatched support for customers wanting to minimize business downtime and ensure a high return on investment. The service agreement includes annual calibration (where relevant), replacement accessories, repairs with priority service, and access to loaner units during repairs. Gold support is included for select discounted products or can be purchased separately. Contact your Fluke Networks representative today to find out more.

Read more:

[www.flukenetworks.com/content/gold-product-support](http://www.flukenetworks.com/content/gold-product-support)

\*Terms and conditions apply. The discount offered under this promotion is valid on purchases of qualifying products made from Fluke's authorized distributors only. Our authorized distributors are free to provide additional price discounts and, thus, higher end-customer savings. Promotion sponsor: Fluke Europe BV. For more information, call: +44-(0)20-79420721, +31-(0)20-7132984, or email: [info@flukenetworks.com](mailto:info@flukenetworks.com)

