



Purchase Fluke 376, 377 or 378 FC True-RMS Clamp Meter



Receive FREE Fluke Insulated Hand Tools Starter Kit Valued at \$328.00

PQ indicator senses power quality issues related to voltage, current and power factor automatically, making it easy to determine if it's an upstream or downstream problem. (Fluke 378 FC Only)

NEW

Fluke 377 FC and 378 FC Clamp Meters with FieldsenseTM

Complete 3-phase measurements

The NEW Fluke 377 FC and 378 FC Clamp Meters are the first handheld clamp meters with FieldSense[™] technology where voltage and current can be measured simultaneously with the clamp jaw, enhancing safety and productivity.

Improve the workflow efficiency by making 3 phase measurements 50% faster! Simply clamp the jaw over each of the three phase conductors and get a full set of phase-to-phase voltage and current measurements on the clamp.

1100

Fluke Electrical Testers



Fluke T6 Series Deals

Purchase Fluke T6-600 or T6-1000 Electrical Tester



Receive FREE Fluke 1AC-A1-II VoltAlert™ Electrical Tester

Valued at \$86.00

NEW

Fluke T6 Electrical Testers

See voltage and current simultaneously

Measure with confidence with the Fluke T6-1000 PRO Electrical Tester – the newest addition to the popular Fluke T6 Electrical Tester family. Take more measurements in less time while using safer work practices. The T6-1000 PRO now comes included with the Fluke H-T6 Holster and heavy-duty crocodile clip as a complete package.

Visual continuity™ the screen turns green when you have continuity between the test in addition to the beeper (T6-1000 PRO only)

FieldSense™ technology for AC voltage, current and frequency measurements without making electrical contact to live voltage

Fluke T6-1000 PRO Deal

Purchase T6-1000 PRO Electrical Tester



Receive FREE Fluke 1AC-A1-II VoltAlert™ Electrical Tester + Fluke TPAK Magnetic Hanger

Valued at \$182.00

Fluke Digital Multimeters

Limited Time Price Drop



NEW

The Fluke 110 Digital Multimeter under \$200! That's 21% off the Fluke 110 Digital

Multimeter for a limited time.

Now Only \$180.00 excl. GST



Fluke 179 True-RMS Digital Multimeter

- True RMS voltage and current measurements
- 0.09% basic accuracy
- 6000 count resolution
- Temperature measurements



Fluke 87V MAX True-RMS Digital Multimeter

- Waterproof, dustproof IP67 case withstands drops up to 4-metres
- Supports accurate measurements on VFDs using a low-pass filter
- Captures intermittents as fast as 250 µS with Peak Capture

Fluke 11X Series Deal



Purchase Fluke 115, 116 or 117 Digital Multimeter



Valued at \$121.00

Fluke 179 Deal



Purchase Fluke 179 True-RMS Digital Multimeter

Receive FREE Fluke TLK225 Master

Fluke TLK225 Master Accessory Set Valued at \$308.00

Fluke 87V MAX Deal



Purchase Fluke 87V MAX Industrial Multimeter



Receive FREE Fluke TLK289 Industrial Master Test Lead Set

Valued at \$345.00

Fluke Front Line Infrared Cameras



NEW

New and Improved Infrared Cameras Optimal resolution, easy to use

Detect issues before they become problems with Fluke thermal cameras.

- Let thermal inspection be part of your everyday tasks with our entry level PTi120 and TiS20+ cameras
- Take clear, in-focus images with both manual and • fixed focus capabilities in our new TiS55+/TiS75+
- Dew-point calculation in the TiS75+ helps you detect moisture/water in the air for facility inspections









	PTi120 (First Generation)	TiS20+/ Ti20+ MAX	TiS60+	TiS55+	TiS75+
Key Features					
Infrared Resolution	120 × 90	120 × 90	320 × 240	256 × 192	384 × 288
Temperature Range	-20°C to 150°C (400°C for TiS20+ MAX)		-20°C to 400°C	-20°C to 550°C	
IFOV with Standard Lens (spatial resolution)	7.6 mRad, D:S 130:1		1.86 mRad, D:S 532:1	1.91 mRad	
Field of View	50° H >	< 38° V	34.1° H × 25.6° V	28° H × 20° V	42° H × 30° V
Minimum Focus Distance	22.8 cm	50 cm	46 cm	50 cm	
LaserSharp Auto Focus	Fixed Focus			Manual Focus	
Advanced Manual Focus	Fixed Focus			Manual Focus	
Fluke Connect® App Compatible	Yes*, connect your camera to your smartphone, and images taken automatically upload to the Fluke Connect® app for saving and sharin				
IR-Fusion Technology	AutoBlend continuous 0% to 100%. Adds the context of the visible details to your infrared image				
Battery Life	≥ 2 hours continuous (without WiFi)	≥ 5 hours continuous (without WiFi)	4 hours continuous use per battery pack	3.5 hours continuous (without Wifi)	
Warranty	Two years (standard)				
Receive free		+			



Receive FREE Fluke 417D Laser Distance Meter Valued at \$189.00



Fluke 417D Laser Distance Meter + C1600 Hard Case Valued at \$329.00



Receive FREE Fluke a3001 FC Wireless iFlex® AC **Current Module** Valued at \$430.00



Receive FREE Fluke a3001 FC Wireless iFlex[®] AC **Current Module** Valued at \$430.00



Receive FREE Fluke 376 FC True-RMS **Clamp Meter** Valued at \$1,029.00

How to redeem your FREE gift:

1. Purchase a selected Fluke test tool in this promotion between 17th May and 30th June 2021

2. Redeem online at www.fluke.co/EOFY21 before COB 14th July 2021

Sponsored by Fluke Australia Pty Ltd. Tool prices listed within this flyer are in Australian Dollars (AUD) excluding GST. Prices listed are Fluke Australia's recommended trade price and are correct at time of print. Final pricing is at the discretion of the participating authorised Fluke Distributor or Wholesaler. Price drop for the Fluke 110 and Fluke PTi120 are only available within the promotional period from 17th May 2021 to 30th June 2021 and will be reinstated from 1st July 2021 or until stocks last. Terms and conditions: Giff with purchase is available for all purchases of a "Qualifying Fluke Purchase" made from an authorised participating Fluke Distributor or Wholesaler within Australia, between 17th May 2021 and 30th June 2021, or until stocks last. Redemption requests must be submitted within 14 days of purchase. In order to redeem your gift, the redemption form must be completed in its entirety with a copy of your receipt/invoice that may only be submitted once per redemption. Offers cannot be combined with any other discounts, promotions or other special offers. Allow 6-8 weeks for delivery. Please note there may be delays pertaining to the ongoing COVID-19 pandemic which may extend this estimated delivery timeframe. The offers in this promotion are only available to Australian Desidents. The offers in this promotion are only available to Australian Residents. Fluke Australia reserves the rights to modify the contents of this promotion at any time for any reason without notice.

Fluke Insulated Hand Tool Kits

Bundle & Save

Save up to 10% when you purchase in a kit



Fluke T6 Electrical Tester + Insulated Hand Tools Starter Kit - IBT6K



Fluke 376 FC Clamp Meter + Insulated Hand Tools Starter Kit - IB376K



Fluke 87V Industrial Multimeter + Insulated Hand Tools Starter Kit - IB875K



Fluke Pack30 Backpack + Insulated Hand Tools Starter Kit - IKPK7




Fluke 117 Electrician's Multimeter + Insulated Hand Tools Starter Kit - IB117K



Insulated Hand Tools Starter Kit - IKST7

Fluke Acoustic Imaging



Fluke ii900 Industrial Acoustic Imager ROI at a glance

Quickly and accurately locate air, gas and vacuum leaks in compressed air systems; even in loud environments. Specifically designed for noisy production facilities the new SoundSight[™] technology provides a straightforward, intuitive maintenance solution.

- Detects a 2.5 cm³/sec leak at 7 bar from up to 10 metres
- Operation range up to >50 metres
- Frequency band of 2 kHz to 52 khz
- Long battery life: 6 hours

