

# Tested. Trusted. Ready for Anything.

Save up to 68,000 DKK on Fluke Networks' most advanced fiber testing and certification solutions – built for accuracy, speed and confidence in the toughest environments.

Contact us  
for your offer  
today

Promotional period: 02.03.2026 – 26.06.2026

Limited-time savings on best-selling fiber testing solutions. Choose the tools that match your workflow from inspection and certification to advanced troubleshooting.



### CertiFiber™ Pro Quad OLTS Kit

A complete solution for fast, accurate certification of singlemode and multimode fiber links to industry standards.

Item no. 4955805  
Part no. CFP2-100-Q/GLD INT

Save 23,293 DKK



### OptiFiber™ Pro OTDR Kit

A troubleshooting solution that locates faults, loss, and reflections in fiber links.

Item no. 4955462  
Part no. OFP2-100QI/GLD INT

Save 25,284 DKK



### CertiFiber™ Pro Add-On + Fiber Inspection Kit

An upgrade kit that adds fiber certification and inspection capabilities to an existing Versiv™ mainframe and remote test setup.

Item no. 6022929  
Part no. CFP-Q-ADD + FI-1000-KIT

Save 9,760 DKK



### FiberInspector™ FI-3000 + Tip Kit

An advanced single and multifiber inspection tool for quickly checking and documenting connector cleanliness and condition.

Item no. 6137122  
Part no. FI-3000 + FI1000-TIP-KIT

Save 4,467 DKK



### DSX2-5000QI CableAnalyzer™ Kit

A cable certification solution for testing copper and fiber networks up to 10 Gigabit Ethernet.

Item no. 4955074  
Part no. DSX2-5000QI/G INT

Save 27,147 DKK



### DSX2-8000QOI CableAnalyzer™ Kit

An advanced all-in-one certification kit combining copper, fiber certification, and fiber inspection in a single solution.

Item no. 4954610  
Part no. DSX2-8000QOI/G INT

Save 68,050 DKK



### DSX2-8000QI CableAnalyzer™ Kit

A high-performance cable certification solution designed for high-speed networks.

Item no. 4954687  
Part no. DSX2-8000QI/G INT

Save 29,854 DKK

Savings shown against regular list prices. Savings vary by configuration.

Fluke Networks test equipment is everywhere – supporting hyperscale data centers and smart cities through to transport, utilities and renewable energy infrastructure. When performance and accuracy matter and failure isn't an option, network professionals around the world rely on Fluke Networks.

Our fiber testing solutions are tested in the most demanding conditions and are ready for anything your network demands today, and in the future.

## Fiber: Why choose Fluke Networks?

Built for network professionals who can't afford failure:

- Deliver accurate, standards-based fiber testing and certification the first time
- Have confidence in every job by reducing rework, retesting and costly callbacks
- Protect your reputation and build trust with professional reporting in the field
- Scale confidently as fiber networks grow in speed, density and complexity

From offshore wind farms to the world's largest data centers, Fluke Networks has you covered.



## CertiFiber™ Max: Fiber Certification, Pushed Further

Designed for today's high-performance high density multi-fiber networks, CertiFiber™ Max builds on decades of fiber expertise to meet growing demands for MPO/MMC testing at high speed across a wide range of MPO/MMC fiber counts and connector arrays.

### Key benefits:

- Faster certification for MPO/MMC singlemode fiber (multimode coming soon)
- Fast, clear, accurate results you can trust
- Intuitive workflows that reduce training time
- Built to support evolving fiber standards and architectures

When networks are growing faster than ever, CertiFiber™ Max helps you stay ahead.

## CertiFiber™ Max

Fiber Testing, Maximized



## Reduce Risk with Premium Care – Gold Support

Most kits include Premium Care – Gold to protect your investment. Premium Care ensures your fiber tools are always ready when you need them.


### Gold support reduces total cost of ownership by:

- Eliminating unexpected service and support charges
- Covering repair or replacement of damaged accessories
- Including annual calibration or performance testing
- Providing loan units to minimize downtime

Less downtime and fewer surprises will give you and your team more confidence on every job.

## PremiumCare

Uptime Protection by



From extreme environments to everyday installations, Fluke Networks fiber solutions are tested, trusted, and ready for anything.

- Deliver professional results
- Win more business
- Support the next wave of digital transformation

Discover the fiber solutions that professionals rely on. **Contact Fluke Networks** to learn more.



Fluke. Keeping your world up and running.™

FlukeNetworks.com

©2026 Fluke Corporation  
Specification subject to change without notice  
260139-en

Modification of this document is not permitted without written permission from Fluke Corporation.