

## 80 Series V Industrial True-RMS Multimeter with Temperature

### Accuracy and diagnostic functions for maximum industrial productivity



The new Fluke 87V has improved measurement functions, troubleshooting features, resolution and accuracy to solve more problems on motor drives, in plant automation, power distribution, and electro-mechanical equipment. The 87V operates very similar to the classic 87, but with more problem-solving power, safety, convenience and impact protection.

#### Features for maximum productivity

- Unique function for accurate voltage and frequency measurements on adjustable speed motor drives and other electrically noisy equipment (87V)
- Built-in thermometer conveniently allows you to take temperature readings without having to carry a separate instrument (87V)
- Large digit display with bright, two-level backlight makes the 80 Series V significantly easier to read than older models

**NEW!** 87V/E2 Industrial Electrician Combo Kit makes troubleshooting more productive with standard meter hanging accessory for hands-free operation, soft case for protection and storage, 1.5 m heat resistant silicone test leads and more.

#### Electrical safety

All inputs are protected to Category III, 1000 V and Category IV 600 V. They can withstand impulses in excess of 8,000 V and reduce risks related to surges and spikes.



### Specifications

Function	Range and resolution	Basic accuracy	
		83V	87V
DC Volts	600.0 mV, 6.000 V, 60.00 V, 600.0 V, 1000 V	0.1 %	0.05 %
AC Volts	600.0 mV, 6.000 V, 60.00 V, 600.0 V, 1000 V	0.5 %	0.7 % (True-rms)
DC Current	600.0 μA, 6000 μA, 60.00 mA, 600.0 mA, 6.000 A, 10.00 A	0.4 %	0.2 %
AC Current	600.0 μA, 6000 μA, 60.00 mA, 600.0 mA, 6.000 A, 10.00 A	1.2 %	1.0 % (True-rms)
Temperature (excl. probe)	-200 to 1090 °C (-328 to 1994 °F)	—	1.0 %
80BK Temperature Probe	-40 to 260 °C (-40 to 500 °F)	—	2.2 °C or 2 %
Resistance	600.0 Ω, 6.000 kΩ, 60.00 kΩ, 600.0 kΩ, 6.000 MΩ, 60.00 MΩ	0.4 %	0.2 %
Capacitance	10.00 nF, 100.0 nF, 1.000 μF, 10.00 μF, 100.0 μF, 9,999 μF	1.0 %	1.0 %
Frequency	199.99 Hz, 1.9999 kHz, 19.999 kHz, 199.99 kHz	0.005 %	0.005 %



## Comparison chart

Feature	83V	87V
True-rms ac voltage and current for accurate measurements on non linear signals		•
Selectable filter for accurate voltage and frequency measurements on motor drives		•
0.05 % dc accuracy		•
4-1/2 digit mode for precise measurements		•
Built-in thermometer lets you carry one less tool		•
Large display digits and two-level bright white backlight for increased visibility	•	•
10,000 µF capacitance range for components and motor caps	•	•
Peak capture to record transients as fast as 250 µs		•
Measure up to 1000 V ac and dc	•	•
Measure up to 10 A, 20 A for up to 30 seconds	•	•
Auto and manual ranging for maximum flexibility	•	•
Analog bargraph	•	•
Resistance, continuity and diode test	•	•
Frequency to 200 kHz and % duty cycle	•	•
Min/Max and average recording to capture variations automatically	•	•
Relative mode to remove test lead resistance from low ohms measurements	•	•
Improved sleep mode for long battery life	•	•
Access door for fast battery changes without breaking the calibration seal	•	•
Limited lifetime warranty	•	•
Removable holster with built in test lead and probe storage	•	•
Cat IV 600 V and Cat III 1000 V electrical safety ratings	•	•
Basic test leads and alligator clips	•	•
Bead type thermocouple temperature probe		•

### Included accessories

Every Fluke 80 Series V meter comes packaged with TL75 Test Leads, AC72 Alligator Clips, holster, 9 V battery (installed), temperature probe (87V only) CD-ROM (user's manual and technical notes) and operator's guide.

### Ordering information

Fluke-83-5	Industrial Multimeter
Fluke-87-5	Industrial True-rms Multimeter with Temperature
Fluke-87-5/E2	Industrial Electrician Combo Kit



### Fluke 87V/E2 Industrial Electrician Combo Kit

Includes special accessories to make industrial troubleshooting even more productive. Save more than \$50\* compared with the individual purchase price.

- A. 87V Industrial Multimeter
- B. **New!** Lightweight soft case for optimal protection and accessory storage
- C. 1.5 m heat resistant silicone test leads
- D. Removable test probes with 4 mm of exposed metal for use on industrial circuits
- E. Retractable long reach alligator clips
- F. Magnetic hanger to position and hold meter to steel surfaces
- G. Temperature probe

\*Savings are noted in US\$

**Fluke.** Keeping your world up and running.™

**Fluke Corporation**  
PO Box 9090, Everett, WA USA 98206

**Fluke Europe B.V.**  
PO Box 1186, 5602 BD  
Eindhoven, The Netherlands

**For more information call:**  
In the U.S.A. (800) 443-5853 or  
Fax (425) 446-5116  
In Europe/M-East/Africa +31 (0) 40 2675 200 or  
Fax +31 (0) 40 2675 222  
In Canada (800)-36-FLUKE or  
Fax (905) 890-6866  
From other countries +1 (425) 446-5500 or  
Fax +1 (425) 446-5116  
Web access: <http://www.fluke.com>

©2006 Fluke Corporation. All rights reserved.  
Printed in U.S.A. 6/2006 2137623 D-EN-N Rev B