

Tested. Trusted. Ready for Anything.

Save up to 101,000 NOK on Fluke Networks' most advanced fiber testing and certification solutions – built for accuracy, speed and confidence in the toughest environments.

Contact us
for your offer
today

Promotional period: 02.03.2026 – 26.06.2026

Limited-time savings on best-selling fiber testing solutions. Choose the tools that match your workflow from inspection and certification to advanced troubleshooting.



CertiFiber™ Pro Quad OLTS Kit

A complete solution for fast, accurate certification of singlemode and multimode fiber links to industry standards.

Item no. 4955805
Part no. CFP2-100-Q/GLD INT

Save 34,851 NOK



OptiFiber™ Pro OTDR Kit

A troubleshooting solution that locates faults, loss, and reflections in fiber links.

Item no. 4955462
Part no. OFP2-100QI/GLD INT

Save 37,830 NOK



CertiFiber™ Pro Add-On + Fiber Inspection Kit

An upgrade kit that adds fiber certification and inspection capabilities to an existing Versiv™ mainframe and remote test setup.

Item no. 6022929
Part no. CFP-Q-ADD + FI-1000-KIT

Save 14,602 NOK



FiberInspector™ FI-3000 + Tip Kit

An advanced single and multifiber inspection tool for quickly checking and documenting connector cleanliness and condition.

Item no. 6137122
Part no. FI-3000 + FI1000-TIP-KIT

Save 6,679 NOK



DSX2-5000QI CableAnalyzer™ Kit

A cable certification solution for testing copper and fiber networks up to 10 Gigabit Ethernet.

Item no. 4955074
Part no. DSX2-5000QI/G INT

Save 40,616 NOK



DSX2-8000QOI CableAnalyzer™ Kit

An advanced all-in-one certification kit combining copper, fiber certification, and fiber inspection in a single solution.

Item no. 4954610
Part no. DSX2-8000QOI/G INT

Save 101,816 NOK



DSX2-8000QI CableAnalyzer™ Kit

A high-performance cable certification solution designed for high-speed networks.

Item no. 4954687
Part no. DSX2-8000QI/G INT

Save 44,668 NOK

Savings shown against regular list prices. Savings vary by configuration.

Fluke Networks test equipment is everywhere – supporting hyperscale data centers and smart cities through to transport, utilities and renewable energy infrastructure. When performance and accuracy matter and failure isn't an option, network professionals around the world rely on Fluke Networks.

Our fiber testing solutions are tested in the most demanding conditions and are ready for anything your network demands today, and in the future.

Fiber: Why choose Fluke Networks?

Built for network professionals who can't afford failure:

- Deliver accurate, standards-based fiber testing and certification the first time
- Have confidence in every job by reducing rework, retesting and costly callbacks
- Protect your reputation and build trust with professional reporting in the field
- Scale confidently as fiber networks grow in speed, density and complexity

From offshore wind farms to the world's largest data centers, Fluke Networks has you covered.



CertiFiber™ Max: Fiber Certification, Pushed Further

Designed for today's high-performance high density multi-fiber networks, CertiFiber™ Max builds on decades of fiber expertise to meet growing demands for MPO/MMC testing at high speed across a wide range of MPO/MMC fiber counts and connector arrays.

Key benefits:

- Faster certification for MPO/MMC singlemode fiber (multimode coming soon)
- Fast, clear, accurate results you can trust
- Intuitive workflows that reduce training time
- Built to support evolving fiber standards and architectures

When networks are growing faster than ever, CertiFiber™ Max helps you stay ahead.

CertiFiber™ Max

Fiber Testing, Maximized



Reduce Risk with Premium Care – Gold Support

Most kits include Premium Care – Gold to protect your investment. Premium Care ensures your fiber tools are always ready when you need them.

Gold support reduces total cost of ownership by:

- Eliminating unexpected service and support charges
- Covering repair or replacement of damaged accessories
- Including annual calibration or performance testing
- Providing loan units to minimize downtime

Less downtime and fewer surprises will give you and your team more confidence on every job.

PremiumCare

Uptime Protection by 



From extreme environments to everyday installations, Fluke Networks fiber solutions are tested, trusted, and ready for anything.

- Deliver professional results
- Win more business
- Support the next wave of digital transformation

Discover the fiber solutions that professionals rely on. **Contact Fluke Networks** to learn more.



Fluke. Keeping your world up and running.™

FlukeNetworks.com

©2026 Fluke Corporation
Specification subject to change without notice
260139-en

Modification of this document is not permitted without written permission from Fluke Corporation.